



MASTER PL-C 4 Pin

MASTER PL-C 18W/830/4P 1CT/5X10BOX

MASTER PL-C is an efficient medium-wattage compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General information	
Cap-Base	G24Q-2 [G24q-2]
Life to 50% Failures Preheat (Nom)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	90 %
Light technical	
Color Code	830 [CCT of 3000K]
Luminous Flux (Nom)	1200 lm
Luminous Flux (Rated) (Nom)	1200 lm
Color Designation	Warm White (WW)

Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	67 lm/W
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	83 %
LLMF 8000 h Rated	81 %
LLMF 12000 h Rated	81 %
Operating and electrical	
Power (Nom)	16.5 W
Lamp Current (Nom)	0.230 A

MASTER PL-C 4 Pin

Temperature

Design Temperature (Nom) 28 °C

Controls and dimming

Dimmable Yes

Mechanical and housing

Cap-Base Information 4 Pins

Approval and application

Mercury (Hg) Content (Nom) 1.4 mg

Energy Consumption kWh/1000 h 20 kWh

Product data

Full product code 871150062333100

Order product name MASTER PL-C 18W/830/4P 1CT/5X10BOX

EAN/UPC - Product 8711500623331

Order code 927907283001

Numerator - Quantity Per Pack 1


Numerator - Packs per outer box 50

Material Nr. (12NC) 927907283001

Net Weight (Piece) 55.300 g

ILCOS Code FSQ-18/30/1B-E-G24q=2


Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 18W/830/4P 1CT/5X10CC	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm

MASTER PL-C 18W/830/4P 1CT/5X10CC

Photometric data




LDPB_PLC4P_830-Spectral power distribution B/W



LDPO_PLC4P_830-Spectral power distribution Colour


MASTER PL-C 4 Pin

Lifetime



LDLE_PLC4P_0001-Life expectancy diagram

LDLE_PLC4P_0002-Life expectancy diagram



LDLM_PLC4P_0001-Lumen maintenance diagram

