



MASTER PL-C 4 Pin

MASTER PL-C 18W/840/4P 1CT/5X10BOX

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 4 parallel narrow fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap-Base	G24q-2	Dimmable	Yes
Light Technical		Approval and Application	
Color Code	840 [CCT of 4000K]	Mercury (Hg) Content (Nom)	1.4 mg
Luminous Flux	1,200 lm	Energy Consumption kWh/1000 h	20 kWh
Color Designation	Cool White (CW)	Product Data	
Correlated Color Temperature (Nom)	4000 K	Order product name	MASTER PL-C 18W/840/4P 1CT/5X10BOX
Luminous Efficacy (rated) (Nom)	67 lm/W	Full product name	MASTER PL-C 18W/840/4P 1CT/5X10BOX
Color rendering index (CRI)	82	Full product code	871869960686200
Operating and Electrical		Local code description	MPLC18W8404P
Power Consumption	18.0 W	Order code	927907284065
Lamp Current (Nom)	0.230 A	Material Nr. (12NC)	927907284065
		Local order code	MPLC18W8404P
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8718699606862

MASTER PL-C 4 Pin


Numerator - Packs per outer box	50
EAN/UPC - Case	8718699606886

Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 18W/840/4P 1CT/ 5X10BOX	27.1 mm	27.1 mm	109.5 mm	128.0 mm	142.9 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-C 18W/840/4P 1CT/5X10BOX

Lifetime



Life Expectancy Diagram - MASTER PL-C 18W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-C 18W/840/4P 1CT/5X10BOX

MASTER PL-C 4 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-C 18W/840/4P 1CT/5X10BOX

