


PHILIPS

Lighting



MASTER PL-C 4 Pin

MASTER PL-C 26W/827/4P 1CT/5X10CC

省電型精巧螢光燈管精巧型長電弧低壓水銀放電燈管套管內含 4 個平行細長螢光燈管

产品数据

基本資訊	
接口	G24Q-3 [G24q-3]
至 50% 故障預熱的使用時間 (標稱)	13000 h
額定 LSF (預熱 2000 小時), 3 小時	99 %
額定 LSF (預熱 4000 小時), 3 小時	98 %
額定 LSF (預熱 8000 小時), 3 小時	97 %
額定 LSF (8000 小時), 3 小時	90 %
照明科技	
色碼	827 [CCT of 2700K]
光通量 (標稱)	1800 lm
光通量 (額定) (標稱)	1800 lm
色彩名稱	白熾 白色
相關色溫 (標稱)	2700 K
光效 (額定) (標稱)	67 lm/W
演色性指數 (標稱)	82
額定 SLMF (2000 小時)	92 %
額定 SLMF (4000 小時)	87 %
額定 SLMF (6000 小時)	83 %
額定 SLMF (8000 小時)	81 %
運作和電氣	
Power (Rated) (Nom)	26.0 W
燈具電流 (標稱)	0.335 A
溫度	
設計溫度 (標稱)	28 °C


控制調光	
可調光	Yes
機械和殼體	
接口資訊	4P
應用	
能源效益標籤 (EEL)	A
汞 (Hg) 含量 (標稱)	1.4 mg
能源消耗 kWh/1000 h	29 kWh
產品參數	
完整產品碼	871150062328700
訂購產品名稱	MASTER PL-C 26W/827/4P 1CT/5X10CC
EAN/UPC - 產品	8711500623287
訂購代碼	927907382701
分子 - 各件數量	1
分子 - 每一外盒內件數	50
材質編號(12NC)	927907382701
淨重 (件)	60.400 g
ILCOS Code	FSQ-26/27/1B-E-G24q=3

MASTER PL-C 4 Pin

安全提示

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


二维绘图




PL-C 26W/827/4P

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C 26W/827/4P 1CT/5X10CC	27.1 mm	27.1 mm	130.5 mm	149.0 mm	163.9 mm

光度数据





LDPB_PLC4P_827-Spectral power distribution B/W



LDPO_PLC4P_827-Spectral power distribution Colour

寿命



LDLE_PLC4P_0002-Life expectancy diagram

MASTER PL-C 4 Pin

壽命

