

PL-L Long 4-Pin Base

PL-L 40W/841/4P/RS/IS 1CT/25

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum effciency and sleek design solutions are required.

Product data


| General Information | | | |
|------------------------------------|--------------------|--|--|
| Cap-Base | 2G11 | | |
| Life to 50% Failures (Nom) | 10,000 hour(s) | | |
| | | | |
| Light Technical | | | |
| Color Code | 841 [CCT of 4100K] | | |
| Luminous Flux | 3,500 lm | | |
| Color Designation | Cool White (CW) | | |
| Correlated Color Temperature (Nom) | 4100 K | | |
| Luminous Efficacy (rated) (Nom) | 87 lm/W | | |
| Color rendering index (CRI) | 82 | | |
| | | | |
| Operating and Electrical | | | |
| Power Consumption | 36.3 W | | |
| Lamp Current (Nom) | 0.320 A | | |
| Voltage (Nom) | 126 V | | |
| | | | |

| Voltage (Nom) | 126 V | | |
|---------------------------------|------------------------------|--|--|
| | | | |
| Controls and Dimming | | | |
| Dimmable | Yes | | |
| | | | |
| Product Data | | | |
| Order product name | PL-L 40W/841/4P/RS/IS 1CT/25 | | |
| Full product name | PL-L 40W/841/4P/RS/IS 1CT/25 | | |
| Order code | 927908008429 | | |
| Material Nr. (12NC) | 927908008429 | | |
| Numerator - Quantity Per Pack | 1 | | |
| EAN/UPC - Product/Case | 046677111809 | | |
| Numerator - Packs per outer box | 25 | | |
| EAN/UPC - Case | 50046677111804 | | |
| | | | |

Datasheet, 2023, December 6 data subject to change


PL-L Long 4-Pin Base

Dimensional drawing



| Product | D (max) | D1 (max) | A (max) | B (max) | C (max) |
|------------------------------|---------|----------|---------|---------|----------|
| PL-L 40W/841/4P/RS/IS 1CT/25 | 39 mm | 18 mm | 540 mm | 565 mm | 571.6 mm |

Photometric data



Spectral Power Distribution Colour - PL-L 40W/841/4P/RS/IS 1CT/25



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.