



PL-L Long 4-Pin Base

PL-L 40W/835/4P/RS/IS 1CT/25

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

| General Information | |
|------------------------------------|--------------------|
| Cap-Base | 2G11 [2G11] |
| Life to 50% Failures (Nom) | 10,000 hour(s) |
| Light Technical | |
| Color Code | 835 [CCT of 3500K] |
| Luminous Flux | 3,500 lm |
| Color Designation | White (WH) |
| Correlated Color Temperature (Nom) | 3500 K |
| Luminous Efficacy (rated) (Nom) | 87 lm/W |
| Color rendering index (CRI) | 82 |
| Operating and Electrical | |
| Power Consumption | 40 W |
| Lamp Current (Nom) | 0.320 A |
| Voltage (Nom) | 126 V |

| Voltage (Nom) | 126 V |
|---------------------------------|------------------------------|
| Controls and Dimming | |
| Dimmable | Yes |
| Product Data | |
| Order product name | PL-L 40W/835/4P/RS/IS 1CT/25 |
| Full product name | PL-L 40W/835/4P/RS/IS 1CT/25 |
| Order code | 300434 |
| Material Nr. (12NC) | 927908083529 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677111793 |
| Numerator - Packs per outer box | 25 |
| EAN/UPC - Case | 50046677111798 |


PL-L Long 4-Pin Base

Dimensional drawing



| Product | D (max) | D1 (max) | A (max) | B (max) | C (max) |
|------------------------------|-------------|----------|-------------|-------------|-------------|
| PL-L 40W/835/4P/RS/IS 1CT/25 | 1-9/16 inch | 3/4 inch | 21-1/4 inch | 22-1/4 inch | 22-1/2 inch |

Photometric data



Spectral Power Distribution Colour - PL-L 40W/835/4P/RS/IS 1CT/25

