



PL-T Triple 4-Pin Base Energy Advantage

PL-T 42W/830/XEW/A/4P/ALTO 33W

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	GX24Q-4 [GX24q-4]
Features	ALTO® (ALTO)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	2,300 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	69 lm/W


Color rendering index (CRI)	>80
Operating and Electrical	
Power Consumption	34.5 W
Lamp Current (Nom)	0.320 A
Controls and Dimming	
Dimmable	Yes

PL-T Triple 4-Pin Base Energy Advantage

Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	PL-T 42W/830/XEW/A/4P/ALTO 33W
Full product name	PL-T 42W/830/XEW/A/4P/ALTO 33W
Order code	220269


Material Nr. (12NC)	927908183020
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677220266
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677220261

Dimensional drawing



Product	D (max)	B (max)	C (max)
PL-T 42W/830/XEW/A/4P/ALTO 33W	41.0 mm	145.0 mm	160.7 mm

Photometric data



Spectral Power Distribution Colour - PL-T 42W/830/XEW/A/4P/ALTO 33W

