



PL-L Energy Advantage

PL-L 40W/830/XEW/4P/IS 25W

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data


General Information		Controls and Dimming	
Base	2G11 [2G11]	Dimmable	Yes
Life to 50% Failures Preheat (Nom)	20000 h		
Light Technical		Mechanical and Housing	
Color Code	830 [CCT of 3000K]	Cap-Base Information	4P
Initial lumen (Nom)	2600 lm		
Color Designation	Warm White (WW)	Approval and Application	
Lumen Maintenance 10000 h (Nom)	92 %	Energy Efficiency Label (EEL)	A
Lumen Maintenance 2000 h (Nom)	96 %	Mercury (Hg) Content (Nom)	1.4 mg
Lumen Maintenance 5000 h (Nom)	95 %	Product Data	
Correlated Color Temperature (Nom)	3000 K	Order product name	PL-L 40W/830/XEW/4P/IS 25W
Color Rendering Index (Nom)	>80	EAN/UPC - Product	046677209131
Operating and Electrical		Order code	209130
Power (Rated) (Nom)	29.0 W	Numerator - Quantity Per Pack	1
Lamp Current (Nom)	0.285 A	Numerator - Packs per outer box	25
		Material Nr. (12NC)	927908383021
		Net Weight (Piece)	140.000 g

PL-L Energy Advantage

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050


Dimensional drawing




Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
PL-L 40W/830/XEW/4P/IS 25W	39.0 mm	18.0 mm	539.2 mm	565.0 mm	571.6 mm

PL-L 40W/830/4P

Photometric data



Lightcolour /830



Lightcolour /830

