



# MASTER PL-L 4 Pin

## MASTER PL-L 55W/840/4P 1CT/25

MASTER PL-L is a medium to high-wattage linear compact fluorescent lamp, typically used for general-illumination ceiling luminaires in retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. It is designed for operation on electromagnetic as well as electronic HF control gear and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Operating and Electrical	
Cap-Base	2G11	Power Consumption	55.0 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	0.525 A
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	4,800 lm	Approval and Application	
Color Designation	Cool White (CW)	Mercury (Hg) Content (Nom)	2.0 mg
Correlated Color Temperature (Nom)	4000 K	Energy Consumption kWh/1000 h	61 kWh
Luminous Efficacy (rated) (Nom)	87 lm/W		
Color rendering index (CRI)	82		

MASTER PL-L 4 Pin

Product Data	
Order product name	MASTER PL-L 55W/840/4P 1CT/25
Full product name	MASTER PL-L 55W/840/4P 1CT/25
Full product code	871150061542841
Order code	927908708472
Material Nr. (12NC)	927908708472


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500615428
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500615527

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 55W/840/4P 1CT/25	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 55W/840/4P 1CT/25

