



Actinic BL PL-L Secura

PL-L 36W/10/4P Secura 1CT/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL PL-L Secura lamps are perfect for attracting insects. With the compact PL-L product format in a variety of wattages, new attractive designs are possible. Furthermore, these lamps have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Product data

General Information		Voltage (Nom)	
Base	2G11 [2G11]	108 V	
Main Application	SECURA (SE)	Mechanical and Housing	
Life to 50% Failures (Nom)	10000 h	Cap-Base Information	4 Pins (4P)
Light Technical		Approval and Application	
Color Code	10	Mercury (Hg) Content (Max)	2.0 mg
Chromaticity Coordinate X (Nom)	228	Mercury (Hg) Content (Nom)	1.8 mg
Chromaticity Coordinate Y (Nom)	215	UV	
UV Depreciation at 2000 h	20 %	UV-A Radiation 100Hr (IEC)	7.7 W
UV Depreciation at 5000 h	40 %	Product Data	
Operating and Electrical		Order product name	PL-L 36W/10/4P SECURA 1CT/25
Power (Rated) (Nom)	36 W	EAN/UPC - Product	8718291194439
Lamp Current (Nom)	0.440 A	Order code	285049

Actinic BL PL-L Secura


Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927909121001

Net Weight (Piece)	133.000 g
--------------------	-----------

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050


Dimensional drawing




PL-L 36W/10/4P SECURA

Product	D1 (max)	D (max)	C1	A (max)	B (max)	C (max)
PL-L 36W/10/4P	27 mm	40 mm	20.0	404.2 mm	430.0 mm	436.6 mm
SECURA 1CT/25			mm			

Photometric data



Lightcolor /10, /110 & /210



Lightcolor /10, /110 & /210

