



# MASTER PL-L 4 Pin

## MASTER PL-L 80W/830/4P 1CT/25

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 2 parallel fluorescent tubes

### Product data

General Information	
Cap base	2G11 [ 2G11]
Life to 50% failures preheat (nom.)	20000 h
System description	High Frequency [ High Frequency (HF)]
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	98 %
LSF Preheat 8000 h Rated	97 %
LSF Preheat 16000 h Rated	82 %
LSF Preheat 20000 h Rated	50 %
Light Technical	
Colour code	830 [ CCT of 3,000 K]
Luminous flux (nom.)	6000 lm
Luminous flux (rated) (nom.)	6000 lm
Colour designation	Warm white (WW)
Correlated colour temperature (nom.)	3000 K
Luminous efficacy (rated) (nom.)	75 lm/W
Color rendering index (nom.)	>80
LLMF 2000 h Rated	95 %
LLMF 4000 h Rated	94 %
LLMF 6000 h Rated	93 %
LLMF 8000 h Rated	92 %
LLMF 12000 h Rated	91 %
LLMF 16000 h Rated	90 %

LLMF 20000 h Rated	90 %
Operating and Electrical	
Power (Rated) (Nom)	80 W
Lamp current (nom.)	0.555 A
Temperature	
Design temperature (nom.)	30 °C
Controls and Dimming	
Dimmable	yes
Mechanical and Housing	
Cap base information	4P
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	2.0 mg
Energy Consumption kWh/1000 h	88 kWh
Product Data	
Full product code	871150086708740
Order product name	MASTER PL-L 80W/830/4P 1CT/25
EAN/UPC – product	8711500867087
Order code	86708740

# MASTER PL-L 4 Pin


Local Code	80PLL830
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	927909583070

Net weight (piece)	140.000 g
ILCOS Code	FSDH-80/30/1B-L/P-2G11

## Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## Dimensional drawing




PL-L 80W/830/4P HF

Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 80W/830/4P 1CT/25	39.0 mm	18.0 mm	539.2 mm	565 mm	571.6 mm

## Photometric data



Lightcolour /830



Lightcolour /830

## MASTER PL-L 4 Pin

