



# MASTER PL-R Eco 4 Pin

## MASTER PL-R ECO 17W/840/4P 1CT/5X10BOX

MASTER PL-R Eco is an extremely efficient compact fluorescent lamp for downlight applications. It consists of six parallel tubes with a new innovative 'twist and lock' lamp base, designed for operation with electronic gear. The MASTER PL-R Eco contains the original bridge technology invented and patented by Philips. This guarantees optimum performance in the application and results in significantly higher efficacies than with regular compact fluorescent lamps. On top of that, MASTER PL-R Eco lamps offer more than double the service life of a standard compact fluorescent lamp, thanks to superior lumen maintenance. The 'twist and lock' lamp base provides easy and safe (dis-)mounting and sturdy fixation in the luminaire.

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General information	
Cap base	GR14Q-1 [ GR14q-1]
Life to 50% failures preheat (nom.)	24000 h
LSF preheat 2,000 hours rated	99 %
LSF preheat 4,000 hours rated	99 %
LSF preheat 6,000 hours rated	99 %
LSF preheat 8,000 hours rated	98 %

LSF preheat 16,000 hours rated	94 %
LSF preheat 20,000 hours rated	87 %
	Sphere
Light technical	
Colour Code	841 [ CCT of 4100K (841)]
Luminous flux (nom.)	1200 lm

## MASTER PL-R Eco 4 Pin

Luminous flux (rated) (nom.)	1250 lm
Colour designation	Cool White (CW)
Luminous efficacy (@ max. lumen, rated) (max.)	81 lm/W
Chromaticity coordinate X (nom.)	0.38
Chromaticity coordinate Y (nom.)	0.38
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	70 lm/W
Colour rendering index (nom.)	80
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	94 %
LLMF 6000 h Rated	93 %
LLMF 8000 h Rated	92 %
LLMF 12000 h Rated	91 %
LLMF 16000 h Rated	90 %
LLMF 20000 h Rated	89 %

### Operating and electrical

Power (Rated) (Nom)	17.7 W
Lamp current (nom.)	0.150 A

### Temperature

Design temperature (nom.)	35 °C
---------------------------	-------

### Controls and dimming

Dimmable	Yes
----------	-----

### Mechanical and housing

Cap-base information	4P
----------------------	----


### Approval and application

Energy Efficiency Class	G
Mercury (Hg) content (max.)	1.4 mg
Mercury (Hg) content (nom.)	1.4 mg
Energy consumption kWh/1,000 hours	18 kWh
	423323

### Product data

Full product code	871150026604070
Order product name	MASTER PL-R Eco 17W/840/4P 1CT/5X10BOX
EAN/UPC – product	8711500266040
Order code	26604070
SAP numerator – quantity per pack	1
Local code description	MASTER PL-R Eco 17W/840/4P 1CT/5X10BOX
Numerator – packs per outer box	50
SAP material	927910084050
Net Weight (Piece)	83.000 g
ILCOS code	FSM6H-17/40/1B-L/P-GR14q=1

## Dimensional drawing




MASTER PL-R Eco 17W/840/4P 1CT/5X10BOX


Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-R Eco 17W/840/4P 1CT/5X10BOX	41.0 mm	121.7 mm	142.0 mm	148.6 mm

# MASTER PL-R Eco 4 Pin

## Photometric data




LDPB\_PLR4P\_840-Spectral power distribution B/W




Lightcolour /840


## Lifetime



LDLE\_PLR4P\_0001-Life expectancy diagram



LDLE\_PLR4P\_0002-Life expectancy diagram



LDLM\_PLR4P\_0001-Lumen maintenance diagram

## MASTER PL-R Eco 4 Pin

