



# MASTER PL-T TOP 4 Pin

## MASTER PL-T TOP 26W/830/4P 1CT/5X10CC

Energy saving compact fluorescent lamp  
Compact long-arc low-pressure mercury discharge lamp  
Envelope consists of 6 parallel narrow fluorescent tubes  
Amalgam controlled operation

### Product data

General Information	
Cap base	GX24Q-3 [ GX24q-3]
Life to 50% failures preheat (nom.)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	90 %
Light Technical	
Colour code	830 [ CCT of 3,000 K]
Luminous flux (nom.)	1800 lm
Luminous flux (rated) (nom.)	1725 lm
Colour designation	Warm white (WW)
Correlated colour temperature (nom.)	3000 K
Luminous efficacy (rated) (min.)	66 lm/W
Color rendering index (nom.)	>80
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	88 %
LLMF 6000 h Rated	85 %
LLMF 8000 h Rated	84 %

LLMF 12000 h Rated	81 %
Operating and Electrical	
Power (Rated) (Nom)	26.0 W
Lamp current (nom.)	0.335 A
Temperature	
Design temperature (nom.)	28 °C
Controls and Dimming	
Dimmable	yes
Mechanical and Housing	
Cap base information	4P
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	30 kWh

# MASTER PL-T TOP 4 Pin


Product Data	
Full product code	871150088944770
Order product name	MASTER PL-T TOP 26W/830/4P 1CT/5X10BOX
EAN/UPC – product	8711500889447
Order code	88944770
Local Code	26PLT8304PINTOP
Numerator – quantity per pack	1

Numerator – packs per outer box	50
Material no. (12NC)	927911383069
Net weight (piece)	64.000 g
ILCOS Code	FSM-26/30/1B-E-GX24q=3

## Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## Dimensional drawing




PL-T TOP 26W/830/4P A

Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T TOP 26W/830/4P 1CT/5X10BOX	41 mm	86.7 mm	111.0 mm	126.7 mm

## Photometric data



Lightcolour /830



Lightcolour /830

# MASTER PL-T TOP 4 Pin

## Lifetime

