



MASTER PL-T Xtra 4 Pin

MASTER PL-T Xtra 42W/840/4P 1CT/5X10BOX

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	GX24Q-4 [GX24q-4]	Power Consumption	42.0 W
Flux measurement reference	Sphere	Lamp Current (Nom)	0.320 A
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	3,000 lm	Approval and Application	
Color Designation	Cool White (CW)	Energy Efficiency Class	G
Chromaticity Coordinate X (Nom)	0.38	Mercury (Hg) Content (Max)	3 mg
Chromaticity Coordinate Y (Nom)	0.38	Mercury (Hg) Content (Nom)	3.0 mg
Correlated Color Temperature (Nom)	4000 K	Energy Consumption kWh/1000 h	42 kWh
Luminous Efficacy (rated) (Nom)	74 lm/W	EPREL Registration Number	423338
Color rendering index (CRI)	80		

MASTER PL-T Xtra 4 Pin

Product Data	
Order product name	MASTER PL-T Xtra 42W/840/4P 1CT/5X10BOX
Full product name	MASTER PL-T Xtra 42W/840/4P 1CT/5X10BOX
Full product code	871150089749770
Local code description	PLTXTRA42W8404P
Order code	927912684014
Material Nr. (12NC)	927912684014


Local order code	PLTXTRA42W8404P
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500897497
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500897510

Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T Xtra 42W/840/4P 1CT/ 5X10BOX	41.0 mm	120.7 mm	145.0 mm	160.7 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-T Xtra 42W/840/4P 1CT/5X10BOX

Lifetime




Life Expectancy Diagram - MASTER PL-T Xtra 42W/840/4P 1CT/5X10BOX




Life Expectancy Diagram - MASTER PL-T Xtra 42W/840/4P 1CT/5X10BOX

MASTER PL-T Xtra 4 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-T Xtra 42W/840/4P 1CT/5X10BOX



Lumen Maintenance Diagram - MASTER PL-T Xtra 42W/840/4P 1CT/5X10BOX

