



# PL-T Triple 4-Pin Base

## PL-T 57W/835/A/4P

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Product data

General Information	
Base	GX24Q-5 [ GX24q-5]
Life to 50% Failures Preheat (Nom)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	90 %
Light Technical	
Color Code	835 [ CCT of 3500K]
Initial lumen (Nom)	4300 lm
Luminous Flux (Rated) (Nom)	3900 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (Rated) (Min)	76 lm/W
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	88 %
LLMF 6000 h Rated	85 %

LLMF 8000 h Rated	84 %
LLMF 12000 h Rated	81 %
Operating and Electrical	
Power (Rated) (Nom)	51.0 W
Lamp Current (Nom)	0.320 A
Temperature	
Design Temperature (Nom)	28 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	4P
Approval and Application	
Energy Efficiency Label (EEL)	B

## PL-T Triple 4-Pin Base


Mercury (Hg) Content (Nom)	1.4 mg
<b>Product Data</b>	
Order product name	PL-T 57W/835/A/4P
EAN/UPC - Product	046677146320
Order code	146324
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	927914083520
Net Weight (Piece)	101.000 g
ILCOS Code	FSM-57/35/1B-E-GX24q=5

### Warnings and Safety

- Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050


### Dimensional drawing




PL-T ALTO 57W/835/4P A

Product	D (max)	A (max)	B (max)	C (max)
PL-T 57W/835/A/4P	41 mm	157.7 mm	182.0 mm	197.7 mm

### Photometric data




Lightcolor /835




Lightcolor /835

# PL-T Triple 4-Pin Base

## Lifetime



### Lumen Maintenance 3 h and 12 h cycle



### Life Expectancy 3 h cycle

### Life Expectancy 12 h cycle

