



MASTER PL-T 2 Pin

MASTER PL-T 13W/840/2P 1CT/5X10BOX

MASTER PL-T is an efficient compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	GX24D-1 [GX24d-1]	Power Consumption	13 W
Life to 50% Failures (Nom)	10,000 hour(s)	Lamp Current (Nom)	0.170 A
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	No
Luminous Flux	900 lm	Approval and Application	
Color Designation	Cool White (CW)	Mercury (Hg) Content (Nom)	1.4 mg
Correlated Color Temperature (Nom)	4000 K	Energy Consumption kWh/1000 h	17 kWh
Luminous Efficacy (Rated) (Min)	62 lm/W		
Color rendering index (CRI)	82		

MASTER PL-T 2 Pin

Product Data	
Order product name	MASTER PL-T 13W/840/2P 1CT/5X10BOX
Full product name	MASTER PL-T 13W/840/2P 1CT/5X10BOX
Full product code	871150055973970
Order code	927914184071
Material Nr. (12NC)	927914184071


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500559739
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500272133

Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 13W/840/2P 1CT/5X10BOX	41 mm	66.7 mm	91.0 mm	114.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-T 13W/840/2P 1CT/5X10BOX

Lifetime




Life Expectancy Diagram - MASTER PL-T 13W/840/2P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T 13W/840/2P 1CT/5X10BOX

MASTER PL-T 2 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-T 13W/840/2P 1CT/5X10BOX

