
PHILIPS Lighting



MASTER PL-T 2 Pin

MASTER PL-T 18W/827/2P 1CT/5X10BOX

MASTER PL-T is an efficient compact fluorescent lamp, typically used in general downlights for retail, hospitality and office applications demanding higher lighting levels. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base.

Warnings and Safety

- \cdot Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- \cdot Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical			
Cap-Base	GX24D-2 [GX24d-2] 10,000 hour(s)	Power Consumption	18.0 W 0.225 A		
Life to 50% Failures (Nom)		Lamp Current (Nom)			
Light Technical		Controls and Dimming			
Color Code	827 [CCT of 2700K]	Dimmable	No		
Luminous Flux	1,200 lm				
Color Designation	Incandescent White	Approval and Application			
Correlated Color Temperature (Nom)	2700 K	Mercury (Hg) Content (Nom)	1.4 mg		
Luminous Efficacy (Rated) (Min)	67 lm/W	Energy Consumption kWh/1000 h	22 kWh		
Color rendering index (CRI)	82				

MASTER PL-T 2 Pin

Product Data	
Order product name	MASTER PL-T 18W/827/2P 1CT/5X10BOX
Full product name	MASTER PL-T 18W/827/2P 1CT/5X10BOX
Full product code	871150055979170
Order code	927914382771
Material Nr. (12NC)	927914382771


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500559791
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500559814

Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 18W/827/2P 1CT/5X10BOX	41 mm	71.8 mm	96.0 mm	119.2 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-T 18W/827/2P 1CT/5X10BOX

Lifetime






14000

MASTER PL-T 2 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-T 18W/827/2P 1CT/5X10BOX



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, September 19 - data subject to change