



MASTER PL-T 4 Pin

MASTER PL-T 26W/840/4P 1CT/5X10BOX

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Luminous Efficacy (Rated) (Min)	
Cap-Base	GX24Q-3 [GX24q-3]	66 lm/W	
Flux measurement reference	Sphere	Color rendering index (CRI)	
		80	
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Power Consumption	27.2 W
Luminous Flux	1,800 lm	Lamp Current (Nom)	0.300 A
Color Designation	Cool White (CW)	Controls and Dimming	
Chromaticity Coordinate X (Nom)	0.38	Dimmable	Yes
Chromaticity Coordinate Y (Nom)	0.38		
Correlated Color Temperature (Nom)	4000 K		

MASTER PL-T 4 Pin

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	28 kWh
EPREL Registration Number	423348
Product Data	
Order product name	MASTER PL-T 26W/840/4P 1CT/5X10BOX
Full product name	MASTER PL-T 26W/840/4P 1CT/5X10BOX


Full product code	871150061125370
Order code	927914684071
Material Nr. (12NC)	927914684071
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500611253
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500611277

Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 26W/840/4P 1CT/5X10BOX	41.0 mm	86.7 mm	111.0 mm	126.7 mm


Photometric data




Spectral Power Distribution Colour - MASTER PL-T 26W/840/4P 1CT/5X10BOX

MASTER PL-T 4 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-T 26W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T 26W/840/4P 1CT/5X10BOX

Lumen Maintenance Diagram - MASTER PL-T 26W/840/4P 1CT/5X10BOX

