



MASTER TL-D Super 80



MASTER TL-D Super 80 18W/865 1SL/25

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	1,300 lm
Color Designation	Cool Daylight
Chromaticity Coordinate X (Nom)	0.313
Chromaticity Coordinate Y (Nom)	0.337
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	68 lm/W
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	18.2 W

Lamp Current (Nom)	0.360 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	Т8
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Nom)	1.7 mg
Energy Consumption kWh/1000 h	19 kWh
EPREL Registration Number	423367
Product Data	
Order product name	MASTER TL-D Super 80 18W/865 1SL/25
Full product name	MASTER TL-D Super 80 18W/865 1SL/25


Datasheet, 2024, March 6 data subject to change

MASTER TL-D Super 80

Full product code	871150063177040
Order code	927920086544
Material Nr. (12NC)	927920086544
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500631770

Numerator - Packs per outer box	25
EAN/UPC - Case	8711500631787

Dimensional drawing




 Product
 D (max)
 A (max)
 B (max)
 B (min)
 C (max)

 MASTER TL-D Super 80 18W/865
 28 mm
 589.8 mm
 596.9 mm
 594.5 mm
 604 mm


 1SL/25


Photometric data



Spectral Power Distribution Colour - MASTER TL-D Super 80 18W/865 1SL/25

Lifetime






Life Expectancy Diagram - MASTER TL-D Super 80 18W/865 1SL/25

Life Expectancy Diagram - MASTER TL-D Super 80 18W/865 1SL/25

MASTER TL-D Super 80

Lifetime



Lumen Maintenance Diagram - MASTER TL-D Super 80 18W/865 1SL/25

