



# TL-D consumer products

## TL-D 30W/840 1PP/10

The lamp can be operated in existing TL-D luminaire and is available in a wide range of wattages and colors.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	12000 h
Life to 50% Failures (Nom)	15000 h
Life to 50% Failures Preheat (Nom)	20000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	99 %
LSF 6000 h Rated	99 %
LSF 8000 h Rated	99 %
LSF 12000 h Rated	89 %
LSF 16000 h Rated	33 %
LSF 20000 h Rated	2 %
Light Technical	
Color Code	840 [ CCT of 4000K]
Luminous Flux (Nom)	2400 lm
Luminous Flux (Rated) (Nom)	2400 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color Rendering Index (Nom)	>80
LLMF 2000 h Rated	96 %

LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

### Operating and Electrical

Power (Rated) (Nom)	30.0 W
Lamp Current (Nom)	0.360 A

### Temperature

Design Temperature (Nom)	25 °C
--------------------------	-------

### Controls and Dimming

Dimmable	Yes
----------	-----

### Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	36 kWh

## TL-D consumer products

### Product Data


Full product code	871150062265525
Order product name	TL-D 30W/840 1PP/10
EAN/UPC - Product	8711500622655
Order code	927920584019
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	927920584019
Net Weight (Piece)	134.900 g
ILCOS Code	FD-30/40/1B-E-G13

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 30W/840 1PP/10	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm

### TL-D 30W/840

### Photometric data



### Lightcolor /840



### Lightcolor /840

# TL-D consumer products

## Lifetime



MASTER TL-D Super 80 Life Expectancy 3 h cycle

MASTER TL-D Super 80 Life Expectancy 12 h cycle



MASTER TL-D Super 80 Lumen Maintenance 3 h + 12 h cycle

