



# TL-D consumer products



## TL-D 36W/830 1PP/10

The lamp can be operated in existing TL-D luminaire and is available in a wide range of wattages and colors.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

<b>General Information</b>		<b>Lamp Current (Nom)</b>		0.440 A
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	<b>Controls and Dimming</b>		
Flux measurement reference	Sphere	Dimmable	Yes	
Life to 50% Failures (Nom)	15,000 hour(s)	<b>Mechanical and Housing</b>		
<b>Light Technical</b>		Bulb Shape	T8	
Color Code	830 [CCT of 3000K]	<b>Approval and Application</b>		
Luminous Flux	3,350 lm	Energy Efficiency Class	G	
Color Designation	Warm White (WW)	Mercury (Hg) Content (Nom)	1.7 mg	
Chromaticity Coordinate X (Nom)	0.44	Energy Consumption kWh/1000 h	37 kWh	
Chromaticity Coordinate Y (Nom)	0.403	EPREL Registration Number	423378	
Correlated Color Temperature (Nom)	3000 K	<b>Product Data</b>		
Luminous Efficacy (rated) (Nom)	93 lm/W	Order product name	TL-D 36W/830 1PP/10	
Color rendering index (CRI)	82	Full product name	TL-D 36W/830 1PP/10	
<b>Operating and Electrical</b>		Full product code	871150062479625	
Power Consumption	36.8 W			


# TL-D consumer products

Order code	927921083022
Material Nr. (12NC)	927921083022
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500624796


Numerator - Packs per outer box	10
EAN/UPC - Case	8711500625847

## Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/830 1PP/10	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm





## Photometric data



Spectral Power Distribution Colour - TL-D 36W/830 1PP/10

## Lifetime




Life Expectancy Diagram - TL-D 36W/830 1PP/10

Life Expectancy Diagram - TL-D 36W/830 1PP/10

## TL-D consumer products

### Lifetime



Lumen Maintenance Diagram - TL-D 36W/830 1PP/10

