



TL-D consumer products

TL-D 36W/830 1PP/10

The lamp can be operated in existing TL-D luminaire and is available in a wide range of wattages and colors.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	12000 h
Life to 50% Failures (Nom)	15000 h
Life to 50% Failures Preheat (Nom)	20000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	99 %
LSF 6000 h Rated	99 %
LSF 8000 h Rated	99 %
LSF 12000 h Rated	89 %
LSF 16000 h Rated	33 %
LSF 20000 h Rated	2 %
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux (Nom)	3350 lm
Luminous Flux (Rated) (Nom)	3350 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	93 lm/W
Color Rendering Index (Nom)	>80
LLMF 2000 h Rated	96 %

LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical

Power (Rated) (Nom)	36.0 W
Lamp Current (Nom)	0.440 A

Temperature

Design Temperature (Nom)	25 °C
--------------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	42 kWh

TL-D consumer products

Product Data


Full product code	871150062479625
Order product name	TL-D 36W/830 1PP/10
EAN/UPC - Product	8711500624796
Order code	927921083022
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	927921083022
Net Weight (Piece)	135.000 g
ILCOS Code	FD-36/30/1B-E-G13

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/830 1PP/10	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

TL-D 36W/830

Photometric data



Lightcolor /830



Lightcolor /830

TL-D consumer products

Lifetime



MASTER TL-D Super 80 Life Expectancy 3 h cycle

MASTER TL-D Super 80 Life Expectancy 12 h cycle



MASTER TL-D Super 80 Lumen Maintenance 3 h + 12 h cycle

