



MASTER TL-D Super 80



MASTER TL-D Super 80 1m 36W/830 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	15,000 h
Light Technical	
Colour Code	830 [CCT of 3000K]
Luminous Flux	3,070 lm
Colour designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	86 lm/W
Colour rendering index (CRI)	82
Operating and Electrical	
Power Consumption	36.6 W
Lamp current (nom.)	0.560 A


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	T8
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (nom.)	1.7 mg
Energy consumption kWh/1,000 hours	37 kWh
EPREL registration number	423417
Product Data	
Order product name	MASTER TL-D Super 80 1m 36W/830 SLV/25
Full product name	MASTER TL-D Super 80 1m 36W/830 1SL/25
Full EOC	871150055874940
Order code	55874940
Material no. (12 NC)	927923083014
Local order code	M36830NG

MASTER TL-D Super 80

SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500558749
Numerator – packs per outer box	25


EAN/UPC – Case	8711500558756
----------------	---------------

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 1m 36W/830 SLV/25	28 mm	970.0 mm	977.1 mm	974.7 mm	984.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Super 80 1m 36W/830 SLV/25

Lifetime




Life Expectancy Diagram - MASTER TL-D Super 80 1m 36W/830 SLV/25



Life Expectancy Diagram - MASTER TL-D Super 80 1m 36W/830 SLV/25

MASTER TL-D Super 80

Lifetime



Lumen Maintenance Diagram - MASTER TL-D Super 80 1m 36W/830
SLV/25

