



# MASTER TL-D Super 80

## MASTER TL-D Super 80 38W/830 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	12000 h
Life to 50% Failures (Nom)	15000 h
Life to 50% Failures Preheat (Nom)	20000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	97 %
LSF 6000 h Rated	96 %
LSF 8000 h Rated	95 %
LSF 12000 h Rated	89 %
LSF 16000 h Rated	33 %
LSF 20000 h Rated	2 %
Light Technical	
Colour Code	830 [ CCT of 3000K]
Luminous Flux (Nom)	3350 lm
Luminous Flux (Rated) (Nom)	3350 lm
Colour Designation	Warm White (WW)
Colour Temperature, horizontal (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Colour Rendering Index horiz (Nom)	>80
Depreciation 2000 hrs	96 %
LLMF 4000 h Rated	95 %

Depreciation 5000 hrs	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

### Operating and Electrical

Power (Rated) (Nom)	38.0 W
Lamp Current (Nom)	0.430 A

### Temperature

Design Temperature (Nom)	25 °C
--------------------------	-------

### Controls and Dimming

Dimmable	Yes
----------	-----

### Approval and Application

Energy Efficiency Label	A
Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	45 kWh

### Product Data

Full product code	871150055880040
-------------------	-----------------

# MASTER TL-D Super 80


Order product name	MASTER TL-D Super 80 38W/830 SLV/25
EAN/UPC - Product	8711500558800
Order code	55880040
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25

Material Nr. (12NC)	927923583014
Net Weight (Piece)	133.000 g
ILCOS Code	FD-38/30/1B-E-G13

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 38W/830 SLV/25	28 mm	1047.0 mm	1054.1 mm	1051.7 mm	1061.2 mm

### TL-D 38W/830

## Photometric data



### Lightcolour /830



### Lightcolour /830

# MASTER TL-D Super 80

## Lifetime



MASTER TL-D Super 80 Life Expectancy 3 h cycle

MASTER TL-D Super 80 Life Expectancy 12 h cycle



MASTER TL-D Super 80 Lumen Maintenance 3 h + 12 h cycle

