



# MASTER TL-D Super 80 日光燈管

## MASTER TL-D Super 80 38W/840 SLV/25

直徑 26 mm 的螢光燈管

### 产品数据

基本資訊	
接口	G13 [ Medium Bi-Pin Fluorescent]
至 10% 故障的使用時間 (標稱)	12000 h
至 50% 故障的使用時間 (標稱)	15000 h
至 50% 故障預熱的使用時間 (標稱)	20000 h
額定 LSF (預熱 2000 小時), 3 小時	99 %
額定 LSF (預熱 4000 小時), 3 小時	99 %
額定 LSF (預熱 6000 小時), 3 小時	99 %
額定 LSF (預熱 8000 小時), 3 小時	99 %
額定 LSF (預熱 12000 小時), 3 小時	89 %
額定 LSF (預熱 16000 小時), 3 小時	33 %
額定 LSF 20000 小時, 12 小時循環	2 %

照明科技	
色碼	840 [ CCT of 4000K (841)]
光通量 (標稱)	3350 lm
光通量 (額定) (標稱)	3350 lm
色彩名稱	冷白色 (CW)
相關色溫 (標稱)	4000 K
光效 (額定) (標稱)	88 lm/W
演色性指數 (標稱)	>80
額定 SLMF (2000 小時)	96 %
額定 SLMF (4000 小時)	95 %

額定 SLMF (6000 小時)	94 %
額定 SLMF (8000 小時)	93 %
額定 SLMF (12000 小時)	92 %
額定 SLMF (16000 小時)	91 %
額定 SLMF (20000 小時)	90 %

運作和電氣	
Power (Rated) (Nom)	38.0 W
燈具電流 (標稱)	0.430 A

溫度	
設計溫度 (標稱)	25 °C

控制調光	
可調光	Yes

應用	
能源效益標籤 (EEL)	A
汞 (Hg) 含量 (標稱)	2.0 mg
能源消耗 kWh/1000 h	45 kWh

產品參數	
完整產品碼	871150055883140

# MASTER TL-D Super 80 日光燈管


訂購產品名稱	MASTER TL-D Super 80 38W/840 SLV/25
EAN/UPC - 產品	8711500558831
訂購代碼	927923584014
分子 - 各件數量	1
分子 - 每一外盒內件數	25

材質編號(12NC)	927923584014
淨重 (件)	133.000 g
ILCOS Code	FD-38/40/1B-E-G13

## 安全提示

· A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## 二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 38W/840 SLV/25	28 mm	1047.0 mm	1054.1 mm	1051.7 mm	1061.2 mm

## TL-D 38W/840

## 光度数据



LDPB\_TL-D8\_840\_0001-Spectral power distribution B/W



LDPO\_TL-D8\_840\_0001-Spectral power distribution Colour

# MASTER TL-D Super 80 日光燈管

## 壽命



LDLE\_TL-D8\_0001-Life expectancy diagram

