



MASTER TL-D HF Super 80 日光燈管

MASTER TL-D HF Super 80 16W/840 SLV/25

直徑 26 mm 的螢光燈管與氬氣充填

产品数据

基本資訊	
接口	G13 [Medium Bi-Pin Fluorescent]
至 50% 故障預熱的使用時間 (標稱)	20000 h
系統說明	高頻 [High Frequency (HF)]
額定 LSF (預熱 2000 小時), 3 小時	99 %
額定 LSF (預熱 4000 小時), 3 小時	99 %
額定 LSF (預熱 8000 小時), 3 小時	99 %
額定 LSF (8000 小時), 3 小時	99 %
額定 LSF (預熱 16000 小時), 3 小時	95 %
額定 LSF (預熱 2000 小時), 3 小時	50 %
照明科技	
色碼	840 [CCT of 4000K (841)]
光通量 (標稱)	1400 lm
光通量 (額定) (標稱)	1400 lm
色彩名稱	冷白色 (CW)
相關色溫 (標稱)	4000 K
光效 (額定) (標稱)	87.5 lm/W
演色性指數 (標稱)	>80
額定 SLMF (2000 小時)	96 %
額定 SLMF (4000 小時)	95 %
額定 SLMF (6000 小時)	94 %
額定 SLMF (8000 小時)	93 %

額定 SLMF (12000 小時)	92 %
額定 SLMF (16000 小時)	91 %
額定 SLMF (20000 小時)	90 %
運作和電氣	
Power (Rated) (Nom)	16.0 W
燈具電流 (標稱)	0.255 A
溫度	
設計溫度 (標稱)	25 °C
控制調光	
可調光	Yes
應用	
能源效益標籤 (EEL)	A
汞 (Hg) 含量 (標稱)	2.0 mg
能源消耗 kWh/1000 h	20 kWh
產品參數	
完整產品碼	871150063147340
訂購產品名稱	MASTER TL-D HF Super 80 16W/840 SLV/25
EAN/UPC - 產品	8711500631473

MASTER TL-D HF Super 80 日光燈管


訂購代碼	927924084023
分子 - 各件數量	1
分子 - 每一外盒內件數	25
材質編號(12NC)	927924084023

淨重 (件)	71.000 g
ILCOS Code	FDH-16/40/1B-L/P-G13-26/600

安全提示

- Special electronic gear must be used
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



二维绘图



TL-D HF 16W/840

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D HF Super 80 16W/840 SLV/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

光度数据



MASTER TL-D HF Super 80 日光燈管

壽命

