



MASTER TL-D HF Super 80 日光燈管

MASTER TL-D HF Super 80 32W/830 SLV/25

直徑 26 mm 的螢光燈管與氬氣充填

安全提示

- Special electronic gear must be used
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


产品数据

一般資訊	
燈座基底	G13 [Medium Bi-Pin Fluorescent]
照明技術	
色碼	830 [CCT of 3000K]
光通量	3,200 lm
色彩名稱	暖白光 (WW)
相關色彩溫度 (規範)	3000 K
光效 (額定) (標準)	100 lm/W
演色性指數 (CRI)	>80
運轉與電力	
耗電量	32.0 W
燈具電流 (標稱)	0.255 A
控制與調光	
可調光	是

機械與外罩	
燈泡形狀	T8 [26 mm (T8)]
認證與應用	
汞 (Hg) 含量 (標稱)	2.0 mg
能源消耗 kWh/1000 h	38 kWh
產品資料	
下訂產品名稱	MASTER TL-D HF Super 80 32W/830 SLV/25
完整產品名稱	MASTER TL-D HF Super 80 32W/830 SLV/25
完整產品代碼	871150063150340
訂單代碼	927924583023
材質 Nr. (12NC)	927924583023
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500631503
分子 - 每一外盒包裝	25
EAN/UPC - 箱	8711500631510


MASTER TL-D HF Super 80 日光燈管

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D HF Super 80 32W/830 SLV/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

光度数据




Spectral Power Distribution Colour - MASTER TL-D HF Super 80 32W/830 SLV/25

壽命




Life Expectancy Diagram - MASTER TL-D HF Super 80 32W/830 SLV/25



MASTER TL-D HF Super 80 日光燈管

壽命



Lumen Maintenance Diagram - MASTER TL-D HF Super 80 32W/830
SLV/25

