



TL5 Essential HE Super 80

TL5 Essential 14W/830 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.

Product data


General Information	
Cap-Base	G5
Nominal lifetime	15000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1350 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	14.3 W
Lamp Current (Nom)	0.170 A

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg
Product Data	
Order product name	TL5 Essential 14W/830 1SL/40
Full product name	TL5 Essential 14W/830 1SL/40
Full product code	871150057031455
Order code	927925983058
Material Nr. (12NC)	927925983058
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500570314
Numerator - Packs per outer box	40

TL5 Essential HE Super 80


EAN/UPC - Case	8711500570321
----------------	---------------

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 14W/830 1SL/40	17.0 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

Photometric data



Spectral Power Distribution Colour - TL5 Essential 14W/830 1SL/40

