



TL5 Essential HE Super 80

TL5 Essential 14W/830 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.
- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.


Product data

General Information		Controls and Dimming	
Cap-Base	G5 [G5]	Dimmable	No
Nominal lifetime	15,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	830 [CCT of 3000K]	Bulb Shape	T5 [16 mm (T5)]
Luminous Flux	1,350 lm		
Color Designation	Warm White (WW)	Approval and Application	
Correlated Color Temperature (Nom)	3000 K	Mercury (Hg) Content (Nom)	2.0 mg
Luminous Efficacy (rated) (Nom)	88 lm/W		
Color rendering index (CRI)	82	Product Data	
Operating and Electrical		Order product name	TL5 Essential 14W/830 1SL/40
Power Consumption	14.3 W	Full product name	TL5 Essential 14W/830 1SL/40
Lamp Current (Nom)	0.170 A	Full product code	871150057031455
		Order code	927925983058
		Material Nr. (12NC)	927925983058
		Numerator - Quantity Per Pack	1

TL5 Essential HE Super 80


EAN/UPC - Product/Case	8711500570314
Numerator - Packs per outer box	40
EAN/UPC - Case	8711500570321

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 14W/830 1SL/40	17.0 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

Photometric data



Spectral Power Distribution Colour - TL5 Essential 14W/830 1SL/40

