



TL5 Essential HE Super 80

TL5 Essential 14W/840 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturised lighting solution with high reliability at low price.

Product data

General Information		LLMF 2000 h Rated	
Cap base	G5 [G5]	LLMF 4000 h Rated	92 %
Life to 50% failures preheat (nom.)	20000 h	LLMF 6000 h Rated	91 %
LSF Preheat 2000 h Rated	98 %	LLMF 8000 h Rated	90 %
LSF Preheat 4000 h Rated	97 %	LLMF 12000 h Rated	88 %
LSF Preheat 6000 h Rated	95 %	LLMF 16000 h Rated	87 %
LSF Preheat 8000 h Rated	93 %	LLMF 20000 h Rated	86 %
LSF Preheat 16000 h Rated	70 %		
LSF Preheat 20000 h Rated	50 %		
Light Technical		Operating and Electrical	
Colour Code	840 [CCT of 4000K (841)]	Technical Lamp Power (Nom)	14.3 W
Lamp Luminous Flux 25°C EL (Nom)	1350 lm	Lamp current (nom.)	0.170 A
Lamp Luminous Flux (Nom)	1260 lm		
Colour Designation	Cool White (CW)	Temperature	
Luminous efficacy (@ max. lumen, rated) (nom.)	96 lm/W	Design temperature (nom.)	30 °C
Colour Temperature, horizontal (Nom)	4000 K		
Lamp Luminous Efficacy EM (Nom)	88 lm/W	Controls and Dimming	
Colour Rendering Index,horiz (Max)	85	Dimmable	no
Colour Rendering Index,horiz (Min)	80		
Colour Rendering Index,horiz (Nom)	82	Approval and Application	
		Energy efficiency label (EEL)	A
		Mercury (Hg) content (nom.)	2.0 mg

TL5 Essential HE Super 80


Energy Consumption kWh/1000 h	15 kWh
Product Data	
Full product code	871150057033855
Order product name	TL5 Essential 14W/840 1SL/40
EAN/UPC – product	8711500570338
Order code	927925984058

Numerator – quantity per pack	1
Numerator – packs per outer box	40
Material no. (12NC)	927925984058
Net weight (piece)	47.500 g

Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.


Dimensional drawing



TL5 ESS 14W/840

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 14W/840 1SL/40	17.0 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

Photometric data



TL5 Essential HE Super 80

