



TL5 Essential HE Super 80

TL5 Essential 14W/865 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.

Product data


Informasi Umum	
Tutup-Dasar	G5
Nominal masa pakai	15.000 jam
Teknis Lampu	
Kode Warna	865 [CCT of 6500K]
Flux Cahaya	1.260 lm
Penandaan Warna	Cool Daylight
Suhu Warna Terkorelasi (Nom)	6500 K
Daya Penerangan (terukur) (Nom)	84 lm/W
Indeks renderasi warna (CRI)	82
Pengoperasian dan Kelistrikan	
Konsumsi Daya	14 W
Arus Lampu (Nom)	0,170 A

Kontrol dan Peredupan	
Dapat diredupkan	Tidak
Mekanis dan Housing	
Bentuk Bohlam	T5 [16 mm (T5)]
Penyetujuan dan Aplikasi	
Kandungan Merkuri (Hg) (Nom)	2,0 mg
Penggunaan Energi kWh/1000 h	15 kWh
Data Produk	
Nama produk pesanan	TL5 Essential 14W/865 1SL/40
Nama lengkap produk	TL5 Essential 14W/865 1SL/40
Kode produk lengkap	871150057035255
Kode urutan	927925986558
No. Material (12NC)	927925986558
Numerator - Jumlah Per Pak	1
EAN/UPC - Produk/Kantung	8711500570352

TL5 Essential HE Super 80


Numerator - Pak per kotak bagian luar	40
EAN/UPC - Kantung	8711500570369

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 14W/865 1SL/40	17,0 mm	549,0 mm	556,1 mm	553,7 mm	563,2 mm

Photometric data



Spectral Power Distribution Colour - TL5 Essential 14W/865 1SL/40

