



MASTER TL5 High Efficiency

MASTER TL5 HE 14W/830 SLV/40

This TL5 lamp (tube diameter 16 mm) has a high luminous efficacy, resulting in low energy consumption. The High Efficiency TL5 lamp offers excellent lumen maintenance and good color rendering. Application areas are offices, industry, public and governmental buildings, schools, hospitals and indoor sports lighting.

Product data

| General Information | | Color Rendering Index (Max) | |
|--|----------------------|-----------------------------|---------|
| Cap-Base | G5 [G5] | Color Rendering Index (Max) | 85 |
| Life to 50% Failures Preheat (Nom) | 24000 h | Color Rendering Index (Min) | 80 |
| Features | na [Not Applicable] | Color Rendering Index (Nom) | >80 |
| System Description | High Efficiency | LLMF 2000 h Rated | 96 % |
| LSF Preheat 2000 h Rated | 99 % | LLMF 4000 h Rated | 95 % |
| LSF Preheat 4000 h Rated | 99 % | LLMF 6000 h Rated | 94 % |
| LSF Preheat 6000 h Rated | 99 % | LLMF 8000 h Rated | 93 % |
| LSF Preheat 8000 h Rated | 99 % | LLMF 12000 h Rated | 92 % |
| LSF Preheat 16000 h Rated | 97 % | LLMF 16000 h Rated | 91 % |
| LSF Preheat 20000 h Rated | 84 % | LLMF 20000 h Rated | 90 % |
| Light Technical | | Operating and Electrical | |
| Color Code | 830 [CCT of 3000K] | Power (Rated) (Nom) | 14 W |
| Luminous Flux (Nom) | 1350 lm | Lamp Current (Nom) | 0.165 A |
| Luminous Flux (Rated) (Nom) | 1200 lm | Temperature | |
| Color Designation | Warm White (WW) | Design Temperature (Nom) | 35 °C |
| Luminous Efficacy (@ Max Lumen, Rated) (Nom) | 99 lm/W | | |
| Correlated Color Temperature (Nom) | 3000 K | | |
| Luminous Efficacy (rated) (Nom) | 86 lm/W | | |

MASTER TL5 High Efficiency

Controls and Dimming

| | |
|----------|-----|
| Dimmable | Yes |
|----------|-----|

Mechanical and Housing

| | |
|----------------------|-------------|
| Cap-Base Information | Green Plate |
|----------------------|-------------|

Approval and Application

| | |
|-------------------------------|--------|
| Energy Efficiency Label (EEL) | A+ |
| Mercury (Hg) Content (Nom) | 1.4 mg |
| Energy Consumption kWh/1000 h | 15 kWh |

Product Data


| | |
|-------------------|-----------------|
| Full product code | 871150063938755 |
|-------------------|-----------------|

| | |
|---------------------------------|------------------------------|
| Order product name | MASTER TL5 HE 14W/830 SLV/40 |
| EAN/UPC - Product | 8711500639387 |
| Order code | 927926083055 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 40 |
| Material Nr. (12NC) | 927926083055 |
| Net Weight (Piece) | 52.000 g |
| ILCOS Code | FDH-14/30/1B-L/P-G5-16/550 |

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




TL5 14W/830/GP HE

| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|------------------------------|---------|----------|----------|----------|----------|
| MASTER TL5 HE 14W/830 SLV/40 | 17 mm | 549.0 mm | 556.1 mm | 553.7 mm | 563.2 mm |

Photometric data




Lightcolor /830



Lightcolor /830


MASTER TL5 High Efficiency

Lifetime



MASTER TL5 HE Life Expectancy 3 h cycle

MASTER TL5 HE Life Expectancy 12 h cycle



MASTER TL5 HE Lumen Maintenance 3 h + 12 h cycle

