



# MASTER TL5 High Efficiency

## MASTER TL5 HE 21W/840 1SL/40

This TL5 lamp (tube diameter 16 mm) has a high luminous efficacy, resulting in low energy consumption. The High Efficiency TL5 lamp offers excellent lumen maintenance and good color rendering. Application areas are offices, industry, public and governmental buildings, schools, hospitals and indoor sports lighting.

### Product data

General Information			
Cap base	G5 [ G5]	Color rendering index (max.)	85
Life to 50% failures preheat (nom.)	24000 h	Color rendering index (min.)	80
Features	na [ Not Applicable]	Color rendering index (nom.)	82
System description	High Efficiency	LLMF 2000 h Rated	96 %
LSF Preheat 2000 h Rated	99 %	LLMF 4000 h Rated	95 %
LSF Preheat 4000 h Rated	99 %	LLMF 6000 h Rated	94 %
LSF Preheat 6000 h Rated	99 %	LLMF 8000 h Rated	93 %
LSF Preheat 8000 h Rated	99 %	LLMF 12000 h Rated	92 %
LSF Preheat 16000 h Rated	97 %	LLMF 16000 h Rated	91 %
LSF Preheat 20000 h Rated	84 %	LLMF 20000 h Rated	90 %
Light Technical		Operating and Electrical	
Colour code	841 [ CCT of 4100K (841)]	Power (Rated) (Nom)	20.6 W
Luminous flux (nom.)	2100 lm	Lamp current (nom.)	0.165 A
Luminous flux (rated) (nom.)	1850 lm		
Colour designation	Cool White (CW)	Temperature	
Luminous efficacy (@ max. lumen, rated) (nom.)	101 lm/W	Design temperature (nom.)	35 °C
Correlated colour temperature (nom.)	4000 K		
Luminous efficacy (rated) (nom.)	90 lm/W		

# MASTER TL5 High Efficiency

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Cap base information	Green Plate
----------------------	-------------

## Approval and Application

Energy efficiency label (EEL)	A+
Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	23 kWh

## Product Data


Full product code	871150063944855
-------------------	-----------------

Order product name	MASTER TL5 HE 21W/840 SLV/40
EAN/UPC – product	8711500639448
Order code	63944855
Numerator – quantity per pack	1
Numerator – packs per outer box	40
Material no. (I2NC)	927926284055
Net weight (piece)	79.200 g
ILCOS Code	FDH-21/40/1B-L/P-G5-16/850

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



## Dimensional drawing



TL5 21W/840/GP HE

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 21W/840 SLV/40	17 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm

## Photometric data



Lightcolour /840

# MASTER TL5 High Efficiency

## Lifetime

