



MASTER TL5 High Efficiency 高效率日光燈管

MASTER TL5 HE 21W/865 SLV/40

直徑 16 mm 的螢光燈管

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	G5
功能	na [Not Applicable]
通量測量參考	Sphere
照明技術	
色碼	865 [CCT of 6500K]
光通量	1,750 lm
色彩名稱	冷日天色
色度坐標 X (標稱)	0.313
色度坐標 Y (Nom)	0.337
相關色彩溫度 (規範)	6500 K
光效 (額定) (標準)	84 lm/W
演色性指數 (CRI)	82

運轉與電力	
耗電量	20.8 W
燈具電流 (標稱)	0.165 A
控制與調光	
可調光	是
機械與外罩	
燈泡形狀	T5
認證與應用	
節能省電等級	G
汞 (Hg) 含量 (標稱)	1.2 mg
能源消耗 kWh/1000 h	21 kWh
EPREL 註冊碼	423456

MASTER TL5 High Efficiency 高效率日光燈管

產品資料	
下訂產品名稱	MASTER TL5 HE 21W/865 SLV/40
完整產品名稱	MASTER TL5 HE 21W/865 SLV/40
完整產品代碼	871150071011655
訂單代碼	927926286555
材質 Nr. (12NC)	927926286555


分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500710116
分子 - 每一外盒包裝	40
EAN/UPC - 箱	8711500867568

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 21W/865 SLV/40	17 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm

光度数据




Spectral Power Distribution Colour - MASTER TL5 HE 21W/865 SLV/40

壽命




Life Expectancy Diagram - MASTER TL5 HE 21W/865 SLV/40



Life Expectancy Diagram - MASTER TL5 HE 21W/865 SLV/40

MASTER TL5 High Efficiency 高效率日光燈管

壽命



Lumen Maintenance Diagram - MASTER TL5 HE 21W/865 SLV/40

