



# TL5 Essential HE Super 80

## TL5 Essential 21W/830 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

### Product data

General Information		LLMF 2000 h Rated		94 %	
Cap-Base	G5 [ G5]	LLMF 4000 h Rated	92 %		
Life to 50% Failures Preheat (Nom)	20000 h	LLMF 6000 h Rated	91 %		
LSF Preheat 2000 h Rated	98 %	LLMF 8000 h Rated	90 %		
LSF Preheat 4000 h Rated	97 %	LLMF 12000 h Rated	88 %		
LSF Preheat 6000 h Rated	95 %	LLMF 16000 h Rated	87 %		
LSF Preheat 8000 h Rated	93 %	LLMF 20000 h Rated	86 %		
LSF Preheat 16000 h Rated	70 %				
LSF Preheat 20000 h Rated	50 %				
Light Technical		Operating and Electrical			
Color Code	830 [ CCT of 3000K]	Power (Rated) (Nom)	20.8 W		
Luminous Flux (Nom)	2100 lm	Lamp Current (Nom)	0.170 A		
Luminous Flux (Rated) (Nom)	1950 lm	Temperature			
Color Designation	Warm White (WW)	Design Temperature (Nom)	30 °C		
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	101 lm/W	Controls and Dimming			
Correlated Color Temperature (Nom)	3000 K	Dimmable	No		
Luminous Efficacy (rated) (Nom)	94 lm/W	Approval and Application			
Color Rendering Index (Max)	85	Energy Efficiency Label (EEL)	A		
Color Rendering Index (Min)	80	Mercury (Hg) Content (Nom)	2.0 mg		
Color Rendering Index (Nom)	82				

# TL5 Essential HE Super 80


Energy Consumption kWh/1000 h	23 kWh
<b>Product Data</b>	
Full product code	871150057037655
Order product name	TL5 Essential 21W/830 1SL/40
EAN/UPC - Product	8711500570376
Order code	927926483058

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927926483058
Net Weight (Piece)	69.500 g

## Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.


## Dimensional drawing



TL5 ESS 21W/830

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 21W/830 1SL/40	17.0 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm

## Photometric data



Lightcolor /830

## TL5 Essential HE Super 80

