



TL5 Essential HE Super 80

TL5 Essential 21W/830 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.


Product data

Informasi Umum	
Tutup-Dasar	G5
Teknis Lampu	
Kode Warna	830 [CCT of 3000K]
Flux Cahaya	2.100 lm
Penandaan Warna	Warm White (WW)
Suhu Warna Terkorelasi (Nom)	3000 K
Daya Penerangan (terukur) (Nom)	94 lm/W
Indeks renderasi warna (CRI)	82
Pengoperasian dan Kelistrikan	
Konsumsi Daya	20,8 W
Arus Lampu (Nom)	0,170 A
Kontrol dan Peredupan	
Dapat diredupkan	Tidak

Mekanis dan Housing	
Bentuk Bohlam	T5
Penyetujuan dan Aplikasi	
Kandungan Merkuri (Hg) (Nom)	2,0 mg
Penggunaan Energi kWh/1000 h	23 kWh
Data Produk	
Nama produk pesanan	TL5 Essential 21W/830 1SL/40
Nama lengkap produk	TL5 Essential 21W/830 1SL/40
Kode produk lengkap	871150057037655
Kode urutan	927926483058
No. Material (12NC)	927926483058
Numerator - Jumlah Per Pak	1
EAN/UPC - Produk/Kantung	8711500570376
Numerator - Pak per kotak bagian luar	40
EAN/UPC - Kantung	8711500570383


TL5 Essential HE Super 80

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 21W/830 1SL/40	17,0 mm	849,0 mm	856,1 mm	853,7 mm	863,2 mm

Photometric data



Spectral Power Distribution Colour - TL5 Essential 21W/830 1SL/40

