



TL5 Essential HE Super 80

TL5 Essential 21W/840 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

产品数据

基本資訊	
接口	G5 [G5]
至 50% 故障預熱的使用時間 (標稱)	20000 h
額定 LSF (預熱 2000 小時), 3 小時	98 %
額定 LSF (預熱 4000 小時), 3 小時	97 %
額定 LSF (預熱 8000 小時), 3 小時	95 %
額定 LSF (8000 小時), 3 小時	93 %
額定 LSF (預熱 16000 小時), 3 小時	70 %
額定 LSF (預熱 2000 小時), 3 小時	50 %

照明科技	
色碼	840 [CCT of 4000K (841)]
光通量 (標稱)	2100 lm
光通量 (額定) (標稱)	1950 lm
色彩名稱	冷 白色 (CW)
光效 (於最大流明, 額定) (標稱)	101 lm/W
相關色溫 (標稱)	4000 K
光效 (額定) (標稱)	94 lm/W
演色性指數 (最大)	85
演色性指數 (最小)	80
演色性指數 (標稱)	82

額定 SLMF (2000 小時)	94 %
額定 SLMF (4000 小時)	92 %
額定 SLMF (6000 小時)	91 %
額定 SLMF (8000 小時)	90 %
額定 SLMF (12000 小時)	88 %
額定 SLMF (16000 小時)	87 %
額定 SLMF (20000 小時)	86 %

運作和電氣	
Power (Rated) (Nom)	20.8 W
燈具電流 (標稱)	0.170 A

溫度	
設計溫度 (標稱)	30 °C

控制調光	
可調光	No

應用	
能源效益標籤 (EEL)	A

TL5 Essential HE Super 80


汞 (Hg) 含量 (標稱)	2.0 mg
產品參數	
完整產品碼	871150057039055
訂購產品名稱	TL5 Essential 21W/840 1SL/40
EAN/UPC - 產品	8711500570390
訂購代碼	927926484058

分子 - 各件數量	1
分子 - 每一外盒內件數	40
材質編號(12NC)	927926484058
淨重 (件)	69.500 g

安全提示

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.


二维绘图



TL5 ESS 21W/840

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 21W/840 1SL/40	17.0 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm

光度数据



LDPO_TL5ESS8_ESS_840-Spectral power distribution Colour

TL5 Essential HE Super 80

