



TL5 Essential HE Super 80

TL5 Essential 21W/840 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

Warnings and Safety


- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.

Product data

General Information		Mechanical and Housing	
Cap-Base	G5	Bulb Shape	T5
Light Technical		Approval and Application	
Color Code	840 [CCT of 4000K]	Mercury (Hg) Content (Nom)	2.0 mg
Luminous Flux	2,100 lm	Product Data	
Color Designation	Cool White (CW)	Order product name	TL5 Essential 21W/840 1SL/40
Correlated Color Temperature (Nom)	4000 K	Full product name	TL5 Essential 21W/840 1SL/40
Luminous Efficacy (rated) (Nom)	94 lm/W	Full product code	871150057039055
Color rendering index (CRI)	82	Order code	927926484058
Operating and Electrical		Material Nr. (12NC)	927926484058
Power Consumption	20.8 W	Numerator - Quantity Per Pack	1
Lamp Current (Nom)	0.170 A	EAN/UPC - Product/Case	8711500570390
Controls and Dimming		Numerator - Packs per outer box	40
Dimmable	No	EAN/UPC - Case	8711500570406


TL5 Essential HE Super 80

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 21W/840 1SL/40	17.0 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm

Photometric data



Spectral Power Distribution Colour - TL5 Essential 21W/840 1SL/40

