



TL5 Essential HE Super 80

TL5 Essential 21W/840 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures Preheat (Nom)	20000 h
LSF Preheat 2000 h Rated	98 %
LSF Preheat 4000 h Rated	97 %
LSF Preheat 6000 h Rated	95 %
LSF Preheat 8000 h Rated	93 %
LSF Preheat 16000 h Rated	70 %
LSF Preheat 20000 h Rated	50 %
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux (Nom)	2100 lm
Luminous Flux (Rated) (Nom)	1950 lm
Color Designation	Cool White (CW)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	101 lm/W
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	94 lm/W
Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82

LLMF 2000 h Rated	94 %
LLMF 4000 h Rated	92 %
LLMF 6000 h Rated	91 %
LLMF 8000 h Rated	90 %
LLMF 12000 h Rated	88 %
LLMF 16000 h Rated	87 %
LLMF 20000 h Rated	86 %

Operating and Electrical

Power (Nom)	20.8 W
Lamp Current (Nom)	0.170 A

Temperature

Design Temperature (Nom)	30 °C
--------------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Approval and Application

Energy Efficiency Label (EEL)	A
-------------------------------	---


TL5 Essential HE Super 80

Mercury (Hg) Content (Nom)	2.0 mg
Product Data	
Full product code	871150057039055
Order product name	TL5 Essential 21W/840 1SL/40
EAN/UPC - Product	8711500570390
Order code	927926484058

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927926484058
Net Weight (Piece)	69.500 g

Warnings and Safety


Dimensional drawing



TL5 ESS 21W/840

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 21W/840 1SL/40	17.0 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm

Photometric data



LDPO_TL5ESS8_ESS_840-Spectral power distribution Colour

