



# TL5 consumer products



## TL5 HE 28W WW 1PP/10

A TL5 lamp is 40% thinner and 5 cm shorter than corresponding TL-D lamp. The lamps are available in 3 wattages and in 2 colors (warm white and cool white)

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G5
Features	na [Not Applicable]
Flux measurement reference	Sphere
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	2,675 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	96 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	28.1 W


Lamp Current (Nom)	0.170 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Energy Efficiency Class	F
Mercury (Hg) Content (Nom)	1.2 mg
Energy Consumption kWh/1000 h	29 kWh
EPREL Registration Number	423459
Product Data	
Order product name	TL5 HE 28W WW 1PP/10
Full product name	TL5 HE 28W WW 1PP/10
Full product code	871150089725125

TL5 consumer products

Order code	927926583032
Material Nr. (12NC)	927926583032
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500897251


Numerator - Packs per outer box	10
EAN/UPC - Case	8711500897268

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 HE 28W WW 1PP/10	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data




Spectral Power Distribution Colour - TL5 HE 28W WW 1PP/10

Lifetime



Life Expectancy Diagram - TL5 HE 28W WW 1PP/10



Life Expectancy Diagram - TL5 HE 28W WW 1PP/10

TL5 consumer products

Lifetime



Lumen Maintenance Diagram - TL5 HE 28W WW 1PP/10

