



MASTER TL5 High Efficiency

MASTER TL5 HE 28W/830 SLV/40

This TL5 lamp (tube diameter 16 mm) has a high luminous efficacy, resulting in low energy consumption. The High Efficiency TL5 lamp offers excellent lumen maintenance and good color rendering. Application areas are offices, industry, public and governmental buildings, schools, hospitals and indoor sports lighting.

Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures Preheat (Nom)	24000 h
Features	na [Not Applicable]
System Description	High Efficiency
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %
Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	>80
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %
Operating and Electrical	
Power (Rated) (Nom)	27.9 W
Lamp Current (Nom)	0.170 A
Temperature	
Design Temperature (Nom)	35 °C
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux (Nom)	2900 lm
Luminous Flux (Rated) (Nom)	2675 lm
Color Designation	Warm White (WW)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	104 lm/W
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	96 lm/W

MASTER TL5 High Efficiency


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	Green Plate
Approval and Application	
Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	31 kWh
Product Data	
Full product code	871150063946255

Order product name	MASTER TL5 HE 28W/830 SLV/40
EAN/UPC - Product	8711500639462
Order code	927926583055
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927926583055
Net Weight (Piece)	104.500 g
ILCOS Code	FDH-28/30/1B-L/P-G5-16/1150

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing




TL5 28W/830/GP HE

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 28W/830 SLV/40	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

Photometric data



Lightcolor /830




Lightcolor /830

MASTER TL5 High Efficiency


Lifetime



MASTER TL5 HE Life Expectancy 3 h cycle



MASTER TL5 HE Life Expectancy 12 h cycle



MASTER TL5 HE Lumen Maintenance 3 h + 12 h cycle

