



# MASTER TL5 High Efficiency Secura

## MASTER TL5 HE Secura 28W/840 UNP/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope and protective coating around the lamp to prevent contamination resulting from breakage

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- It's strongly recommended to replace Secura lamps before or at the moment the specified lamp life (50% failures @ 3 hrs switching cycle) is reached.

### Product data

General Information	
Cap-Base	G5 [G5]
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	2,900 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	96 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	27.9 W
Lamp Current (Nom)	0.170 A


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	31 kWh
Product Data	
Order product name	MASTER TL5 HE Secura 28W/840 UNP/40
Full product name	MASTER TL5 HE Secura 28W/840 UNP/40
Full product code	871150095215855
Order code	95215855

# MASTER TL5 High Efficiency Secura

Material Nr. (12NC)	927926684018
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500952158
Numerator - Packs per outer box	40


EAN/UPC - Case	8711500952165
----------------	---------------

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE Secura 28W/840 UNP/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

## Photometric data




Spectral Power Distribution Colour - MASTER TL5 HE Secura 28W/840 UNP/40

## Lifetime




Life Expectancy Diagram - MASTER TL5 HE Secura 28W/840 UNP/40



Life Expectancy Diagram - MASTER TL5 HE Secura 28W/840 UNP/40

MASTER TL5 High Efficiency Secura

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HE Secura 28W/840 UNP/40

