



MASTER TL5 High Efficiency Secura

MASTER TL5 HE Secura 28W/840 UNP/40

This TL5 High Efficiency Secura lamp (tube diameter 16 mm) has a protective coating that keeps glass and lamp components together in the event of accidental breakage. The lamp is easily identifiable by a blue ring at one end. Application areas are all places where glass shatters can disturb operations and can have an impact on product and people safety, e.g. the food and beverage industry. This lamp is compliant with HACCP regulations and supports HACCP certification.

Warnings and Safety

• COMF-2525

Product data

General Information	
Cap-Base	G5 [G5]
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	2,900 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	96 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	27.9 W
Lamp Current (Nom)	0.170 A


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5 [16 mm (T5)]
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	31 kWh
Product Data	
Order product name	MASTER TL5 HE Secura 28W/840 UNP/40
Full product name	MASTER TL5 HE Secura 28W/840 UNP/40
Full product code	871150095215855
Order code	927926684018
Material Nr. (12NC)	927926684018

MASTER TL5 High Efficiency Secura

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500952158
Numerator - Packs per outer box	40


EAN/UPC - Case	8711500952165
----------------	---------------

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE Secura	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm
28W/840 UNP/40					

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HE Secura 28W/840 UNP/40

Lifetime




Life Expectancy Diagram - MASTER TL5 HE Secura 28W/840 UNP/40



Life Expectancy Diagram - MASTER TL5 HE Secura 28W/840 UNP/40

MASTER TL5 High Efficiency Secura

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HE Secura 28W/840 UNP/40

