



# TL5 Essential HE Super 80

## TL5 Essential 28W/830 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

### Product data

General Information	
Cap-Base	G5 [ G5]
Life to 50% Failures Preheat (Nom)	20000 h
LSF Preheat 2000 h Rated	98 %
LSF Preheat 4000 h Rated	97 %
LSF Preheat 6000 h Rated	95 %
LSF Preheat 8000 h Rated	93 %
LSF Preheat 16000 h Rated	70 %
LSF Preheat 20000 h Rated	50 %
Light Technical	
Color Code	830 [ CCT of 3000K]
Luminous Flux (Nom)	2900 lm
Luminous Flux (Rated) (Nom)	2600 lm
Color Designation	Warm White (WW)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	104 lm/W
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	94 lm/W
Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82

LLMF 2000 h Rated	94 %
LLMF 4000 h Rated	92 %
LLMF 6000 h Rated	91 %
LLMF 8000 h Rated	90 %
LLMF 12000 h Rated	88 %
LLMF 16000 h Rated	87 %
LLMF 20000 h Rated	86 %

Operating and Electrical	
Power (Rated) (Nom)	27.8 W
Lamp Current (Nom)	0.170 A

Temperature	
Design Temperature (Nom)	30 °C

Controls and Dimming	
Dimmable	No

Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	2.0 mg

# TL5 Essential HE Super 80


Energy Consumption kWh/1000 h	31 kWh
<b>Product Data</b>	
Full product code	692341077188600
Order product name	TL5 Essential 28W/830 1SL/40
EAN/UPC - Product	6923410771886
Order code	927926783060

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927926783060
Net Weight (Piece)	0.096 kg

## Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.


## Dimensional drawing



TL5 ESS 28W/830

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 28W/830 1SL/40	17.0 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

## Photometric data



LDPO\_TL5ESS8\_ESS\_830-Spectral power distribution Colour

## TL5 Essential HE Super 80

