



TL5 Essential HE Super 80

TL5 Essential 28W/840 1SL/40

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturised lighting solution with high reliability at low price.

Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.

Product data

General Information		
Cap base	G5 [G5]	
Life to 50% failures preheat (nom.)	20000 h	
LSF preheat 2,000 hours rated	98 %	
LSF preheat 4,000 hours rated	97 %	
LSF preheat 6,000 hours rated	95 %	
LSF preheat 8,000 hours rated	93 %	
LSF preheat 16,000 hours rated	70 %	
LSF preheat 20,000 hours rated	50 %	
Colour Rendering Index,horiz (Max)		85
Colour Rendering Index,horiz (Min)		80
Colour Rendering Index,horiz (Nom)		82
LLMF 2000 h Rated		94 %
LLMF 4000 h Rated		92 %
LLMF 6000 h Rated		91 %
LLMF 8000 h Rated		90 %
LLMF 12000 h Rated		88 %
LLMF 16000 h Rated		87 %
LLMF 20000 h Rated		86 %
Light Technical		
Colour Code	840 [CCT of 4,000 K]	
Lamp Luminous Flux 25°C EL (Nom)	2900 lm	
Lamp Luminous Flux (Nom)	2600 lm	
Colour Designation	Cool White (CW)	
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	104 lm/W	
Colour Temperature, horizontal (Nom)	4000 K	
Lamp Luminous Efficacy EM (Nom)	94 lm/W	
Operating and Electrical		
Technical Lamp Power (Nom)	27.8 W	
Lamp current (nom.)	0.170 A	
Temperature		
Design temperature (nom.)	30 °C	

TL5 Essential HE Super 80

Controls and Dimming

Dimmable	No
----------	----

Approval and Application


Energy efficiency label (EEL)	A+
Mercury (Hg) content (nom.)	2.0 mg
Energy consumption kWh/1,000 hours	31 kWh

Product Data

Full product code	871150057045155
-------------------	-----------------

Order product name	TL5 Essential 28W/840 1SL/40
EAN/UPC – product	8711500570451
Order code	927926784058
SAP numerator – quantity per pack	1
SAP numerator – packs per outer box	40
SAP material	927926784058
Net Weight (Piece)	88.500 g


Dimensional drawing



TL5 ESS 28W/840

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 28W/840 1SL/40	17.0 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

Photometric data



LDPO_TL5ESS8_ESS_840-Spectral power distribution Colour

TL5 Essential HE Super 80

