



MASTER TL5 High Efficiency

MASTER TL5 HE 35W/830 SLV/40

This TL5 lamp (tube diameter 16 mm) has a high luminous efficacy, resulting in low energy consumption. The High Efficiency TL5 lamp offers excellent lumen maintenance and good color rendering. Application areas are offices, industry, public and governmental buildings, schools, hospitals and indoor sports lighting.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap-Base	G5 [G5]	Power Consumption	34.9 W
Features	na [Not Applicable]	Lamp Current (Nom)	0.175 A
Flux measurement reference	Sphere		
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Luminous Flux	3,315 lm		
Color Designation	Warm White (WW)	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	0.44	Bulb Shape	T5 [16 mm (T5)]
Chromaticity Coordinate Y (Nom)	0.403		
Correlated Color Temperature (Nom)	3000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	94 lm/W	Energy Efficiency Class	F
Color rendering index (CRI)	82	Mercury (Hg) Content (Nom)	1.2 mg
		Energy Consumption kWh/1000 h	35 kWh
		EPREL Registration Number	423541

MASTER TL5 High Efficiency

Product Data	
Order product name	MASTER TL5 HE 35W/830 SLV/40
Full product name	MASTER TL5 HE 35W/830 SLV/40
Full product code	871150063950955
Order code	63950955
Material Nr. (12NC)	927927083055


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500639509
Numerator - Packs per outer box	40
EAN/UPC - Case	8711500867667

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 35W/830 SLV/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HE 35W/830 SLV/40

Lifetime



Life Expectancy Diagram - MASTER TL5 HE 35W/830 SLV/40



Life Expectancy Diagram - MASTER TL5 HE 35W/830 SLV/40

MASTER TL5 High Efficiency

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HE 35W/830 SLV/40

