


PHILIPS

Lighting



MASTER TL5 High Efficiency 高效率日光燈管

MASTER TL5 HE 35W/840 SLV/40

直徑 16 mm 的螢光燈管

产品数据

基本資訊	
接口	G5 [G5]
至 50% 故障預熱的使用時間 (標稱)	24000 h
功能	na [Not Applicable]
系統說明	高效率
額定 LSF (預熱 2000 小時), 3 小時	99 %
額定 LSF (預熱 4000 小時), 3 小時	99 %
額定 LSF (預熱 8000 小時), 3 小時	99 %
額定 LSF (8000 小時), 3 小時	99 %
額定 LSF (預熱 16000 小時), 3 小時	97 %
額定 LSF (預熱 2000 小時), 3 小時	84 %
照明科技	
色碼	840 [CCT of 4000K (841)]
光通量 (標稱)	3650 lm
光通量 (額定) (標稱)	3325 lm
色彩名稱	冷白色 (CW)
光效 (於最大流明, 額定) (標稱)	105 lm/W
相關色溫 (標稱)	4000 K
光效 (額定) (標稱)	94 lm/W
演色性指數 (最大)	85

演色性指數 (最小)	80
演色性指數 (標稱)	82
額定 SLMF (2000 小時)	96 %
額定 SLMF (4000 小時)	95 %
額定 SLMF (6000 小時)	94 %
額定 SLMF (8000 小時)	93 %
額定 SLMF (12000 小時)	92 %
額定 SLMF (16000 小時)	91 %
額定 SLMF (20000 小時)	90 %

運作和電氣

Power (Rated) (Nom)	35.5 W
燈具電流 (標稱)	0.175 A

溫度

設計溫度 (標稱)	35 °C
-----------	-------

控制調光

可調光	Yes
-----	-----

MASTER TL5 High Efficiency 高效率日光燈管


機械和殼體	
接口資訊	綠色底座
應用	
能源效益標籤 (EEL)	A+
汞 (Hg) 含量 (標稱)	1.4 mg
能源消耗 kWh/1000 h	38 kWh
產品參數	
完整產品碼	871150063952355

訂購產品名稱	MASTER TL5 HE 35W/840 SLV/40
EAN/UPC - 產品	8711500639523
訂購代碼	927927084055
分子 - 各件數量	1
分子 - 每一外盒內件數	40
材質編號(12NC)	927927084055
淨重 (件)	127.400 g
ILCOS Code	FDH-35/40/1B-L/P-G5-16/1450

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



二维绘图



TL5 HE 35W/840/GP

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 35W/840 SLV/40	17 mm	1449.0 mm	1456.1 mm	1453.7 mm	1463.2 mm

光度数据



MASTER TL5 High Efficiency 高效率日光燈管

壽命

