

PHILIPS

Lighting



MASTER TL5 High Efficiency 高效率日光燈管

MASTER TL5 HE 35W/840 SLV/40

直徑 16 mm 的螢光燈管

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	G5
功能	na [Not Applicable]
通量測量參考	Sphere
照明技術	
色碼	840 [CCT of 4000K]
光通量	3,315 lm
色彩名稱	冷白光 (CW)
色度坐標 X (標稱)	0.38
色度坐標 Y (Nom)	0.38
相關色彩溫度 (視範)	4000 K
光效 (額定) (標準)	94 lm/W
演色性指數 (CRI)	80


運轉與電力	
耗電量	34.9 W
燈具電流 (標稱)	0.175 A
控制與調光	
可調光	是
機械與外罩	
燈泡形狀	T5
認證與應用	
節能省電等級	F
汞 (Hg) 含量 (標稱)	1.2 mg
能源消耗 kWh/1000 h	35 kWh
EPREL 註冊碼	423543

MASTER TL5 High Efficiency 高效率日光燈管

產品資料	
下訂產品名稱	MASTER TL5 HE 35W/840 SLV/40
完整產品名稱	MASTER TL5 HE 35W/840 SLV/40
完整產品代碼	871150063952355
訂單代碼	927927084055
材質 Nr. (12NC)	927927084055


分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500639523
分子 - 每一外盒包裝	40
EAN/UPC - 箱	8711500867681

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 35W/840 SLV/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

光度数据




Spectral Power Distribution Colour - MASTER TL5 HE 35W/840 SLV/40

壽命




Life Expectancy Diagram - MASTER TL5 HE 35W/840 SLV/40



Life Expectancy Diagram - MASTER TL5 HE 35W/840 SLV/40

MASTER TL5 High Efficiency 高效率日光燈管

壽命



Lumen Maintenance Diagram - MASTER TL5 HE 35W/840 SLV/40

