



# MASTER TL5 High Efficiency

## MASTER TL5 HE 35W/865 1SL/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

### Product data

General Information	
Cap base	G5 [ G5]
Life to 50% failures preheat (nom.)	24000 h
Features	na [ Not Applicable]
System description	High Efficiency
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %
Light Technical	
Colour code	865 [ CCT of 6,500 K]
Luminous flux (nom.)	3400 lm
Luminous flux (rated) (nom.)	3100 lm
Colour designation	Cool Daylight
Luminous efficacy (@ max. lumen, rated) (nom.)	98 lm/W
Correlated colour temperature (nom.)	6500 K
Luminous efficacy (rated) (nom.)	87 lm/W
Color rendering index (max.)	85
Color rendering index (min.)	80
Color rendering index (nom.)	82

LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

### Operating and Electrical

Power (Rated) (Nom)	35.5 W
Lamp current (nom.)	0.175 A

### Temperature

Design temperature (nom.)	35 °C
---------------------------	-------

### Controls and Dimming

Dimmable	yes
----------	-----

### Mechanical and Housing

Cap base information	Green Plate
----------------------	-------------

### Approval and Application

Energy efficiency label (EEL)	A+
-------------------------------	----

# MASTER TL5 High Efficiency


Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	38 kWh
<b>Product Data</b>	
Full product code	871150071018555
Order product name	MASTER TL5 HE 35W/865 SLV/40
EAN/UPC – product	8711500710185
Order code	71018555

Local Code	35865
Numerator – quantity per pack	1
Numerator – packs per outer box	40
Material no. (12NC)	927927086555
Net weight (piece)	127.400 g
ILCOS Code	FDH-35/65/1B-L/P-G5-16/1450

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## Dimensional drawing




TL5 35W/865/GP HE

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 35W/865 SLV/40	17 mm	1449.0 mm	1456.1 mm	1453.7 mm	1463.2 mm

## Photometric data



Lightcolour /865



Lightcolour /865

# MASTER TL5 High Efficiency

## Lifetime

