



# MASTER TL5 High Output

## MASTER TL5 HO 49W/827 SLV/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Controls and Dimming	
Cap-Base	G5 [G5]	Dimmable	Yes
Features	na [Not Applicable]		
Light Technical		Mechanical and Housing	
Color Code	827 [CCT of 2700K]	Bulb Shape	T5 [16 mm (T5)]
Luminous Flux	4,900 lumen		
Color Designation	Incandescent White	Approval and Application	
Correlated Color Temperature (Nom)	2700 K	Mercury (Hg) Content (Nom)	1.4 mg
Luminous Efficacy (rated) (Nom)	89 lm/W	Energy Consumption kWh/1000 h	54 kWh
Color rendering index (CRI)	82		
Operating and Electrical		Product Data	
Power Consumption	49.2 W	Full product code	871150064312455
Lamp Current (Nom)	0.255 A	Order product name	MASTER TL5 HO 49W/827 SLV/40
		Order code	927927582755
		Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	40

# MASTER TL5 High Output


Material Nr. (12NC)	927927582755
Full product name	MASTER TL5 HO 49W/827 SLV/40
EAN/UPC - Case	8711500867704

EAN/UPC - Product/Case	8711500643124
------------------------	---------------

## Dimensional drawing


Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 49W/827 SLV/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

## Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 49W/827 SLV/40

## Lifetime




Life Expectancy Diagram - MASTER TL5 HO 49W/827 SLV/40



Life Expectancy Diagram - MASTER TL5 HO 49W/827 SLV/40

# MASTER TL5 High Output

## Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 49W/827 SLV/40

