



MASTER TL5 High Output

MASTER TL5 HO 49W/830 1SL/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General information			
Cap base	G5 [G5]	Luminous flux (rated) (nom.)	4375 lm
Life to 50% failures preheat (nom.)	30000 h	Colour designation	Warm White (WW)
Features	na [Not Applicable]	Luminous Efficacy (@ Max Lumen, Rated) (Nom)	99 lm/W
System description	High Output (HO)	Chromaticity coordinate X (nom.)	0.44
LSF preheat 2,000 hours rated	99 %	Chromaticity coordinate Y (nom.)	0.403
LSF preheat 4,000 hours rated	99 %	Correlated Colour Temperature (Nom)	3000 K
LSF preheat 6,000 hours rated	99 %	Luminous efficacy (rated) (nom.)	89 lm/W
LSF preheat 8,000 hours rated	99 %	Color rendering index (max.)	85
LSF preheat 16,000 hours rated	97 %	Colour-rendering index (min.)	80
LSF preheat 20,000 hours rated	84 %	Colour rendering index (nom.)	82
	Sphere	LLMF 2000 h Rated	96 %
		LLMF 4000 h Rated	95 %
		LLMF 6000 h Rated	94 %
		LLMF 8000 h Rated	93 %
		LLMF 12000 h Rated	92 %
		LLMF 16000 h Rated	91 %
Light technical			
Colour Code	830 [CCT of 3,000 K]		
Luminous flux (nom.)	4375 lm		

MASTER TL5 High Output

LLMF 20000 h Rated	90 %
Operating and electrical	
Power (Rated) (Nom)	49.3 W
Lamp current (nom.)	0.255 A
Temperature	
Design temperature (nom.)	35 °C
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Cap-base information	Green Plate
Bulb shape	T5 [16 mm (T5)]
Approval and application	
Energy Efficiency Class	G

Mercury (Hg) content (nom.)	1.2 mg
Energy consumption kWh/1,000 hours	50 kWh
	423546
Product data	
Full product code	871150063954755
Order product name	MASTER TL5 HO 49W/830 SLV/40
EAN/UPC – product	8711500639547
Order code	63954755
SAP numerator – quantity per pack	1
Numerator – packs per outer box	40
SAP material	927927583055
Copy Net Weight (Piece)	128.700 g
ILCOS code	FDH-49/30/1B-L/P-G5-16/1450


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 49W/830 SLV/40	17 mm	1449.0 mm	1456.1 mm	1453.7 mm	1463.2 mm

MASTER TL5 HO 49W/830 SLV/40

Photometric data





LDPB_TL5-HO8_830-Spectral power distribution B/W



Lightcolour /830


MASTER TL5 High Output

Lifetime



LDLE_TL5-HO8_0001-Life expectancy diagram

LDLE_TL5-HO8_0002-Life expectancy diagram



LDLM_TL5-HO8_0001-Lumen maintenance diagram

